


REVISIONS	
ISSUE	CHANGES
2	CN 27545 C SD 7V0V 85



NOTES:  
1. FOR USE WITH RG-55, 58, 141, 142, 223 & 11T BA 13077A CABLE GROUPS.

HEX SIZES (ACROSS FLATS)				DIE WIDTH		WEB WIDTH	
A	B	C	D	F	G	H	I
.069	.253	.213		.500	.080		.083

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS  $\pm .010$
2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX.
3. PLACE DECIMALS  $\pm .004$
3. NO FILLETS PERMITTED.
4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX.
5. ALL DIMENSIONS PRIOR TO PLATING.
- T. I. R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT EXCEED HALF THE SUM OF THEIR TOLERANCES.

REF:	
FINISH	
SPEC.	
MATL.	
SPEC.	
CRIMP DIE	
DRAWN BG.	DATE 13 OCT 72
APPR.	DATE
KINGS ELECTRONICS	
40 MARBLEDALE ROAD	
TUCKAHOE, N. Y. 10707	
KTH-2061	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[KTH-2061](#)