


REVISIONS	
ISSUE	CHANGES



NOTES:

1. FOR USE WITH BA 13077A & BA 14349 CABLE GROUPS.

HEX SIZES (ACROSS FLATS)				DIE WIDTH	WEB WIDTH		
A	B	C	D	F	G	H	I
.069	.213	.253	—	.620	.080	—	.110

UNLESS OTHERWISE SPECIFIED:

1. TOLERANCES: FRACTIONS & 2 PLACE DECIMALS ± .010
2. REMOVE ALL BURRS, BREAK SHARP EDGES .005 MAX
3. PLACE DECIMALS ± .004
3. NO FILLETS PERMITTED.
4. SURFACE ROUGHNESS 63 MICROINCHES RMS MAX
5. ALL DIMENSIONS PRIOR TO PLATING
- 1.1 R. CONCENTRICITY OF ANY 2 DIAMETERS MAY NOT

DRAWN GINO		DATE 11 AUG 75
APPR	DATE	
KING'S ELECTRONICS		
40 MARBLEDALE ROAD		
TUCKAHOE N Y 10707		
KTH-2161		

CRIMP DIE

REF:

FINISH

SPEC.

MATL.

SPEC.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[KTH-2161](#)