


SD



NOTES:

1. INTERFACE PER MIL-STD-348, FIG. 304-1 AND 304-2.
2. MATERIALS:
INSULATORS: TEFLON, ASTM-D-4894
GASKET: SIL. RUBBER, ZZ-R-765
CENTER CONTACT: BER. COPPER, ASTM-B-196
OUTER CONTACT AND C-RING: PHOS. BRONZE, ASTM-B-103
ALL OTHER METAL PARTS: BRASS, ASTM-B16
3. FINISHES:
CENTER CONTACT: SILVER PLATE PER QQ-S-365
ALL OTHER METAL PARTS: SILVER PLATE PER QQ-S-365
4. ELECTRICAL CHARACTERISTICS
NOMINAL IMPEDANCE: 50 \sim W
FREQUENCY RANGE: DC TO 11 GHz
VOLTAGE RATING: 1000 VOLTS RMS

SD

UG-27C/U

REVISIONS

ISSUE	CHANGES	
	DATE	BY
8	CN 4081 A J.G. 03/30/66	
9	CN 10615 A WLA 12/16/71	
10	CN 17241 C JHP 05/05/77	
11	CN 27408 D SD 09/25/85	
12	CN 38111 C REDRAWN TML 10/24/00	

UG27CU-SD

SCALE: 4:1

APPROX SURFACE AREA

KN-98-01

USED ON

REF: MS-90156 A

ADAPTER, N, M-F

DRAWN	J.G.	DATE	03/30/66
DESIGN		DATE	
APPR.	LI	DATE	03/30/66

KINGS
ELECTRONICS CO., INC.
ROCK HILL, SOUTH CAROLINA 29730

UG-27C/U

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[UG-27 C/U](#)