

NOTES: UNLESS OTHERWISE SPECIFIED

1. MATERIAL SPECIFICATION:

BODY: BRASS PER ASTM B16

RETAINING RING: BERYLLIUM COPPER PER ASTM B194

2. FINISH SPECIFICATION:

BODY: .000030 MIN. GOLD PER ASTM B488 OVER


.000050 MIN. NICKEL PER QQ-N-290

RETAINING RING: .000100 MIN. NICKEL PER QQ-N-290


3. THIS DIMENSION CAN BE .150" MAX AFTER TIN DIP.

REV	DESCRIPTION	BY DATE	APPD
E	REVISED PER ER7306	CWB 04/14/08	CWB

$\phi .175 \pm .002$ [4.45 $\pm$.05]



RECOMMENDED
MOUNTING HOLE



PER ASME Y14.5M-1994
UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN INCHES [MM]
TOLERANCES:
DECIMAL: .XX [X.X] $\pm$.01 [0.3]
.XXX [X.XX] $\pm$.005 [0.13]
.XXXX [X.XXX] $\pm$.XXXX
ANGLES: $\pm$ 2° SCALE: 8:1

Winchester Electronics
Winchester Electronics Corporation
62 Barnes Industrial Road North
Wallingford, Connecticut 06492

CUSTOMER
DRAWING



POWER SNAP
PC BOARD THRU HOLE
40 AMP

DRAWN JED	DATE 10/02/97	APPROVED AT	DATE 10/02/97
APPROVED JM	DATE 10/02/97	APPROVED JM	DATE 10/02/97

A

SD01206

SHT 1 OF 1

REV
E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Winchester Interconnect:](#)

[01206](#)