





|           |                      |          |                                                    |
|-----------|----------------------|----------|----------------------------------------------------|
| PART NAME | PLASTICASE (STYLE D) | PART No. | PC-11480 & PC-11480-A & PC-11480-LG & PC-11480-LGA |
|-----------|----------------------|----------|----------------------------------------------------|



0.218 DIA. BOSS WITH 0.090 DIA. HOLE x 0.218 DEEP - (8) PLACES  
MOUNTING BOSSES USE EITHER M2.5 METRIC OR #4 STD. SHEET METAL SCREWS x 0.188" LG. (NOT SUPPLIED)



**MATERIAL & FINISH:**  
(NO SUFFIX) UL94V-0 FLAME RETARDANT ABS  
DARK GRAY PLASTIC COVERS WITH LIGHT GRAY PLASTIC PANELS.  
(SUFFIX -A) UL94V-0 FLAME RETARDANT ABS  
DARK GRAY PLASTIC COVERS WITH NATURAL FINISH ALUMINUM PANELS.  
(SUFFIX -LG) HIGH-IMPACT ABS  
LIGHT GRAY PLASTIC COVERS WITH BLACK PLASTIC PANELS.  
(SUFFIX -LGA) HIGH-IMPACT ABS  
LIGHT GRAY PLASTIC COVERS WITH NATURAL FINISH ALUMINUM PANELS.  
  
TWO (2) M3 x 0.812" LG. SCREWS SUPPLIED FOR ASSEMBLY.  
  
**NOTE:** ALL DIMENSIONS HAVE ±0.015 TOLERANCE UNLESS OTHERWISE SPECIFIED



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[PC-11480-A](#) [PC-11480-LGA](#) [PC-11480](#) [PC-11480-LG](#)