

PART
NAME

VALU/LINE SERIES CABINET

PART
No.

HC-14106

REVISION
DATE

11-1-07

MATERIAL:

BACK & COVERS _____ 0.050 THICK ALUMINUM
SIDES & INNER BRACKETS _____ 0.090 THICK ALUMINUM
FRONT PANEL _____ 0.125 THICK ALUMINUM
OUTER BRACKETS _____ 11 GA. C.R.S.
HANDLE EXTRUSIONS _____ ALUMINUM

FINISH:







BACK & COVERS _____ PREPAINTED SMOOTH WHITE
SIDES & OUTER BRACKETS _____ WHITE TEXTURED
FRONT PANEL _____ NATURAL (OUTSIDE SURFACE TAPED WITH PVC)
INNER BRACKETS _____ NATURAL
HANDLE EXTRUSIONS _____ CAUSTIC ETCH & CLEAR ANODIZED
FEET _____ BLACK

UNIT SHIPPED UNASSEMBLED.

OUTER BRACKETS FOR MOUNTING IN
STANDARD 19" WIDE CABINETS.

OPTIONAL SELF-ADHESIVE RUBBER FEET (SUPPLIED)

LOAD RATING: 25 LBS. MAX.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[HC-14106](#)