




PART NAME	SHELF ASSEMBLY	PART No.	SA-1719 AND SA-1720
 MATERIAL: SHELF _____ 16 GA. STEEL SUPPORT BRACKETS _____ 12 GA. STEEL FINISH: SHELF & SUPPORT BRACKETS _____ GRAY TEXTURE OR ROYAL BLUE TEXTURE LOAD RATING: 100 LBS. MAX.			
PART No.	DEPTH	PART No.	DEPTH
SA-1719	16.000	SA-1720	20.000
PART NAME	SHELF	PART No.	60-2380
 MATERIAL: 16 GA. STEEL FINISH: SMOOTH BLACK LOAD RATING: 200 LBS. MAX.			
PART NAME	SHELF	PART No.	60-2381
 MATERIAL: 16 GA. STEEL FINISH: SMOOTH BLACK LOAD RATING: 200 LBS. MAX.			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[60-2381](#) [60-2380](#) [SA-1719-RB](#) [SA-1719-GT](#) [SA-1720-GT](#) [1720RB](#) [SA-1720-RB](#)