

PART NAME


ECONOCAB

PART No.


EC-9902 TO EC-9906



TOP VIEW



RUBBER FOOT  
0.625 DIA. x 0.218 HIGH



BOTTOM VIEW

NOTES:

MATERIAL: BODY ASSEMBLY \_\_\_\_\_ 18 GA. STEEL  
 HANDLE \_\_\_\_\_ ABS PLASTIC  
 FOOT \_\_\_\_\_ RUBBER  
 FINISH: BODY ASSEMBLY \_\_\_\_\_ SAND TEXTURE  
 \_\_\_\_\_ BLACK TEXTURE  
 HANDLE \_\_\_\_\_ BLACK  
 FOOT \_\_\_\_\_ BLACK

MOUNTING RAILS ARE PIERCED 0.281 DIA. HOLES  
 ON E.I.A. UNIVERSAL SPACING.

LOAD RATING: 500 LBS. MAX.

PART NO.	DIM. A	DIM. B
EC-9902	9.062	7.062
EC-9903	10.812	8.812
EC-9904	12.562	10.562
EC-9905	14.312	12.312
EC-9906	16.062	14.062

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Bud Industries:

[EC-9902-BT](#) [EC-9902-S](#) [EC-9906-S](#) [EC-9903-BT](#) [EC-9903-S](#) [EC-9904-S](#) [EC-9906-BT](#) [EC-9905-S](#) [EC-9905-BT](#)  
[EC-9904-BT](#)