





**INSIDE BODY DETAILS****TOP VIEW****SECTION A-A**

SIX (6) M4x0.7 PITCH
x 20mm (.787") LG.
STAINLESS STEEL FLAT HEAD
CAPTIVE SCREWS

**BOTTOM VIEW**

Ø .176 x .315 [8.00] DEEP BLIND HOLE (4X)
[4.47]
{ACCEPTS M5 x 10mm (.394") LG.
SELF-TAPPING SCREWS (NOT SUPPLIED)}


**INSIDE COVER DETAILS**

MEETS NEMA 1, 2, 4, 4X, 12, 13 AND IP67 RATINGS




MATERIAL - ALUMINUM ALLOY ADC-12

FINISH - NATURAL (NO SUFFIX PART NO.)
- SMOOTH BLACK (-B SUFFIX PART NO.)

TOLERANCES: ALL HOLE DIAMETERS $\pm .005$ [$\pm .13$]
ALL OTHER DIMENSIONS $\pm .02$ [$\pm .4$]

**DETAIL B
SCALE 4 : 1**

(10X) IN BODY, (8X) IN COVER
{ACCEPTS M3.5 x 6mm (.236") LG.
SELF-TAPPING SCREWS (NOT SUPPLIED)}

**DETAIL C
SCALE 4 : 1****SUGGESTED PC BOARD OR
INTERNAL PANEL LAYOUT**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[ANS-3809](#) [ANS-3809-B](#)