


NOTES:







1. MATERIAL:
BODY - PC & PBC LIGHT GRAY
COVER - PC & PBC LIGHT GRAY
POLYCARBONATE
LATCHES - STAINLESS STEEL
2. UL94 VO(1.5mm) AND 5VA (3mm) FLAMMABILITY
RATING, UV RESISTANT.
3. BOXES DESIGNED TO MEET FOLLOWING STANDARDS:
NEMA 4X, 12 & 13.
4. SERVICE TEMPERATURE -20 TO 70C SUITABLE FOR BOTH
INDOOR AND OUTDOOR APPLIATIONS
5. RMPF POURED GASKET IN COVER
6. COVER IS REMOVABLE
7. DIMENSIONS ARE INCH [MM]

DRAWING FOR REFERENCE


WE RESERVE THE RIGHT TO MAKE CHANGES TO OUR
STANDARD PRODUCTS. PLEASE CONSULT WITH BUD INDUSTRIES
PRIOR TO USING THIS DRAWING FOR DESIGN PURPOSE.




INSIDE VIEW OF BODY
COVER NOT SHOWN



SECTION A-A
SCALE 1 : 6



SECTION B-B
SCALE 1 : 6



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[NBG-20015](#) [NBG-20015-C](#)