








NOTES:

- 1- MATERIAL: BODY - POLYCARBONATE 10% FIBERGLASS REINFORCED
COVER - POLYCARBONATE
UL508 /NEMA TYPE 4X WITH IP-67 TUV RATING & UL-94V0 RATING
- 2- FINISH: BODY - LIGHT GRAY
COVER - LIGHT GRAY OR CLEAR (-C)
- 3- ALL HOLE DIAMETERS HAVE +/- .005(0.13) TOLERANCE
ALL OTHER DIMENSIONS HAVE +/- 0.03(0.76) TOLERANCE UNLESS OTHERWISE SPECIFIED
- 4- CONTINUOUS GASKET IN COVER
- 5- SUPPLIED WITH FOUR M5 x 10mm LG. TRUSS HEAD MACHINE SCREWS
- 6- DIMENSIONS ARE INCH [MM]
- 7- DRAWING FOR REFERENCE
- 8- OPTIONAL ACCESSORIES:
INTERNAL STEEL PANEL - #PTX-11059
INTERNAL PLASTIC PANEL - #PTX-11059-P
MOUNTING BRACKET KIT (STAINLESS STEEL) - #NBX-10922

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[PTQ-11059-C](#) [PTQ-11059](#)