



MATERIAL:
BODY - POLYCARBONATE RESIN 10% GLASS FIBER FILLED
COVER - POLYCARBONATE
COLOR:
BODY - LIGHT GRAY
COVER - LIGHT GRAY OR CLEAR (SUFFIX -C)
UL508 / NEMA TYPE 4X WITH IP-67 TUV RATING & UL-94V0 RATING
CONTINUOUS GASKET IN COVER
SUPPLIED WITH FOUR M5 x 10mm LG. TRUSS HEAD MACHINE SCREWS
DIMENSIONS ARE INCH[MM]
DRAWING FOR REFERENCE
OPTIONAL ACCESSORIES:
INTERNAL STEEL PANEL - #PTX-11064
INTERNAL PLASTIC PANEL - #PTX-11064-P
MOUNTING BRACKET KIT (STAINLESS STEEL) - #NBX-10922

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[PTQ-11064](#) [PTQ-11064-C](#)