

NOTES:

1- MATERIAL: BODY - POLYCARBONATE 10% FIBERGLASS REINFORCED
COVER - POLYCARBONATE
UL508 /NEMA TYPE 4X WITH IP-67 TUV RATING & UL-94V0 RATING

2- FINISH: BODY - LIGHT GRAY
COVER - LIGHT GRAY OR CLEAR (-C)

3- ALL HOLE DIAMETERS HAVE +/- .005(0.13) TOLERANCE
ALL OTHER DIMENSIONS HAVE +/- 0.03(0.76) TOLERANCE UNLESS OTHERWISE SPECIFIED

4- CONTINUOUS GASKET IN COVER




5- SUPPLIED WITH FOUR M5 x 10mm LG. TRUSS HEAD MACHINE SCREWS

6- DIMENSIONS ARE INCH [MM]




7- DRAWING FOR REFERENCE

8- OPTIONAL ACCESSORIES:


INTERNAL STEEL PANEL - #PTX-11073
INTERNAL PLASTIC PANEL - #PTX-11073-P
MOUNTING BRACKET KIT (STAINLESS STEEL) - #NBX-10922




INSIDE VIEW OF COVER



SECTION A-A



INSIDE VIEW OF BODY



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[PTQ-11073](#) [PTQ-11073-C](#)