




NOTES:




- 1- MATERIAL: BODY - POLYCARBONATE 10% FIBERGLASS REINFORCED
COVER - POLYCARBONATE
UL508 /NEMA TYPE 4X WITH IP-67 TUV RATING & UL-94V0 RATING
- 2- FINISH: BODY - LIGHT GRAY
COVER - LIGHT GRAY OR CLEAR (-C)
- 3- ALL HOLE DIAMETERS HAVE +/- .005(0.13) TOLERANCE
ALL OTHER DIMENSIONS HAVE +/- 0.03(0.76) TOLERANCE UNLESS OTHERWISE SPECIFIED
- 4- CONTINUOUS GASKET IN COVER
- 5- SUPPLIED WITH FOUR M5 x 10mm LG. TRUSS HEAD MACHINE SCREWS
- 6- DIMENSIONS ARE INCH [MM]
- 7- DRAWING FOR REFERENCE
- 8- OPTIONAL ACCESSORIES:
INTERNAL STEEL PANEL - #PTX-11076
INTERNAL PLASTIC PANEL - #PTX-11076-P
MOUNTING BRACKET KIT (STAINLESS STEEL) - #NBX-10922




BOTTOM OF BODY



INSIDE VIEW OF COVER

SECTION A-A
SCALE 1 : 4

INSIDE VIEW OF BODY



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[PTQ-11076](#) [PTQ-11076-C](#)