






NOTES:




1. MATERIAL:
BODY - GRAY ABS
COVER - GRAY ABS OR CLEAR (-C SUFFIX) POLYCARBONATE
2. UL508 / NEMA TYPE 4X & 6P WITH IP-67 TUV RATING & UL-94 HB
3. POURED CONTINUOUS GASKET
4. SUPPLIED WITH PLASTIC INTERNAL PANEL - PTX-18492-P
5. DIMENSIONS ARE INCH[MM]
6. OPTIONAL ACCESSORIES:
16 GA INTERNAL MOUNTING PLATE OR ABS
EXTERNAL MOUNTING BRACKETS - NBX-10922, PIP-117-PMB



ISOMETRIC VIEW 1



SECTION A-A
SCALE 1 : 2.75



ISOMETRIC VIEW 2

DRAWING FOR REFERENCE
WE RESERVE THE RIGHT TO MAKE CHANGES TO OUR
STANDARD PRODUCTS. PLEASE CONSULT WITH BUD INDUSTRIES
PRIOR TO USING THIS DRAWING FOR DESIGN PURPOSES.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bud Industries:](#)

[PTR-28492](#) [PTR-28492-C](#)