

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO J.S.T. AND SHALL NOT BE USED OR SHOWN WITHOUT WRITTEN PERMISSION.

4		3		2		1	
ITEM	CONNECTOR PART NO.	DESCRIPTION	IPI CHECK	EOR CHECK	Applicable Tooling		
1	SRSF-82T-250A	RSF CONTACT, BRASS TIN-PLATED			APPLICATOR		
2	UL1015, 16 AWG	BLACK (X2)					

SUGGESTED MATING TAB
NO SCALE

	WITHOUT STABILIZER	WITH STABILIZER
DIM. "A"	2.20 [0.087] MIN.	4.20±0.15 [0.165±0.006]
DIM. "B"	7.40 [0.291] MIN.	7.98 [0.314] MIN.
DIM. "C"	5.90 [0.232] MAX.	(7.6)

MATING TAB NOTES:
4. MAT'L: BRASS.
FINISH: SUGGESTED NO PLATING.

1

2
2

SCALE		CUSTOMER NAME		CUSTOMER PART NO.	
1: 1					
DIMENSIONS		DESCRIPTION			
All dimensions are in MM with a tolerance of +/- 3.0 unless otherwise specified.		2" LIF, POS LOCK, .250, SINGLE-END, DOUBLE-CRIMP LEADS, BRASS TIN-PLATED, F-F			
DRAWN BY		ASSEMBLY PART NO.			
STEVEN PILKINGTON		ASRSF2X16K51B			
CHECKED BY		DRAWING NO. & REVISION		REVISED	
JUSTIN BAKER		GAM-154		3/16/2016	

4		3		2		1	
REV.	DESCRIPTION		DATE	BY			

Applicable Housings	
NO. OF CIRCUITS	KEYLESS HOUSING PART NO.
2	RSFP-2V-00
3	RSFP-3V-00
4	RSFP-4V-00
5	RSFP-5V-00
6	RSFP-6V-00
7	RSFP-7V-00
8	RSFP-8V-00
9	RSFP-9V-00
10	RSFP-10V-00
11	RSFP-11V-00
12	RSFP-12V-00
Other housings and configurations are available. Please contact JST for details.	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JST:](#)

[ASRSF2X16K51B](#)