

8300 Push Button Switches 8(8)A 250Vac & 12(12)A 250Vac



- ▶ Miniature push button
- ▶ 8A Inductive current rating
- ▶ Ratings up to 12(12)A, 250V ac (H suffix)
- ▶ Illuminated and non-illuminated
- ▶ Single and double pole
- ▶ Latching and momentary
- ▶ Slotted actuator for custom buttons
- ▶ Industry standard panel cutout
- ▶ Panel cut out:
19.3 x 12.9



16(4)A 250Vac T85, 1E4 (10,000 Operations)
12(12)A 250Vac T105, 1E4 (10,000 Operations)
8(8)A 250Vac T105, 5E4 (50,000 Operations)
6(6)A 250Vac T125, 5E4 (50,000 Operations)



12A 250Vac DP, 13A 250Vac SP
250Vac 1hp, 125Vac 1/2hp
UL 85°C, file E45221, CSA file LR10990

In house test

10(10)A 250Vac



RoHS compliant

3mm contact gap.
Technical data on pages 4 & 5 (switches), 6 (indicators).


NON-LIT			LIT		
B BLACK	R RED	W WHITE	A AMBER	C CLEAR	G GREEN
			R RED		
				2 125V NEON	3 250V NEON
					7 12V INCANDESCENT

H 8353 J E B R 2 1153W

TERMINAL CODE FUNCTION CODE ACTUATOR CODE BODY CODE BODY COLOR ACTUATOR COLOR LAMP VOLTAGE IF REQUIRED LEGEND & OPTIONS

ORDER FORMAT


TERMINAL



FUNCTION

		1	2	3	4
Approvals & ratings vary with function Single pole switches use terminals 1 & 2 (& 3)					
8300	ON - OFF Single pole				
8301	ON - OFF (momentary ON) Single pole				
8303	ON - OFF with light Single pole				
8304	ON - OFF (momentary ON) with light Single pole				
8350	ON - OFF Double pole				
8351	ON - OFF (momentary ON) Double pole				
8353	ON - OFF with light Double pole				
8354	ON - OFF (momentary ON) with light Double pole				
8355	ON - OFF Single pole Isolated light - switched C, E & M actuators only				
8356	ON - OFF Single pole Isolated light - unswitched C, E & M actuators only				

ACTUATOR





H8350AB ---
T8350AB ---



H8353JE ---
T8353JE ---




H8353EB ---
T8353EB ---



H8353CB ---
T8353CB ---



H8350DB ---
T8350DB ---




H8350HB ---
Example of button

push
switches


BODY

Panel cut-out Bezel
Cut-outs must be punched in the direction of insertion

B Standard body



E Softline style body with radiused bezel



Dimensions for snap-in fixing

Panel thickness	Dimension X
0.75-1.24	19.1/19.2
1.25-1.99	19.3/19.4
2.00-3.00	19.7/19.8

X and V PCB terminals.
Additional dummy terminals may be supplied for extra support.

OPTIONS

H
12(12)A 250Vac switch rating

Finish
Matt finish standard except on J and D actuators which are gloss

Color
Call factory for custom colors
A full range is available for large orders

Legend printing
Select from the examples or call factory for custom legends

Special buttons
Some of the many options are shown
Call the factory for the full range


L167 Protective cover
(designed to IP65)




Snaps on to switch bodies fitted with "A" or "J" style actuators but increases effective panel thickness by 0.8mm

DIMENSIONS (mm)

Actuator A Body B



Actuator J Body E



Spacing between centre of terminals 1 & 3 or 2 & 4 is 10.0mm

Examples of legend printing

() is legend colour B-Black, W-White, R-Red



1153(W)



1152(W)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bulgin:](#)

[H8350ABBR](#)