



BZV03/A0620/09 Datasheet

Product Name // Vertical Power Entry Module 78.7mm C14
Cold Condition Inlet (PX0575) 6.3mm Tab Termination A0620
Filter (6A PS01/A L/C v2) 2 x FX0359 Fuseholders Double
Contact Illuminated Switch Green

 [View Product Page](#)





Panel Thickness: 10, 15, 20, 30mm.
BZV03, BZV04/****/** A = 62.5 With Filter
39.0 Without Filter
BZV05, BZV06/****/** A = 39.0

// Product Description:

- Vertical Power Entry Module 50.8mm/78.7mm
 - C14 Cold Condition Inlet (PX0575)
 - Choice of Termination depending on part code:
 - Part codes prefixed BZV03: 6.3mm Tab
 - Part codes prefixed BZV04: 2.8mm Tab
- Choice of mains filter depending on part code:
 - Part codes containing /Z0000 are unfiltered
 - Choice of mains filter options (part codes containing codes starting /A)
 - Choice of many other options as specified by individual part code, including fuseholders, voltage selectors, indicators, illuminated switches, switch markings, etc
 - Also available in C16 Hot Condition Inlet (PX0595) versions in both Terminations (6.3mm Tab part code BZV05, 2.8mm Tab part code BZV06), Unfiltered only

// General Information:

Product Display Title:	Vertical Power Entry Module 50.8mm/78.7mm
Product Family:	IEC Connectors
Product Series:	Power Entry Modules
Current Max:	6A
Filter Type:	6A PS01/A L/C v2
Function:	C14 Inlets
Iec Connector Components:	None
Iec Connector Mates With:	PX0575
Iec Filter Options:	A0620
Iec Neon Colour:	Green
Iec Vertical Module Height:	78.7mm
Inlet Type:	C14 Cold Condition Inlet
Number Of Fuseholders:	2 x FX0359 Fuseholders
Switch Type:	Double Contact Illuminated
Voltage Max:	250V

// Product PDF Links

 [Power Entry Modules product data](#)

// Product 3D CAD Model Links

 [BZV03/A0620/093D CAD Model](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bulgin:](#)

[BZV03/A0620/09](#)