

Detailed Specifications

Frame Width:	40[mm]
Frame Height:	40[mm]
Frame Depth:	10[mm]
Max. Air Flow:	6.7[CFM]
Max. Air Flow:	0.19[m3 per min]
Max. Static Pressure:	0.2[In H2O]
Max. Static Pressure:	50[Pa]
Fan Speed:	7500[RPM]
Noise:	29[dB]
Life Expectancy:	40 degree C 30,000 Hours[L10]
Bearing Type:	Sleeve Bearing
Nominal Voltage:	5[V]
Operating Voltage - Lower:	4.5[V]
Operating Voltage - Upper:	5.5[V]
Current:	0.17[A]
Input Power:	0.9[W]
Mass:	16[g]
Tach / Locked Rotor Output:	Tach Output
Status:	Active

DC Axial Fans

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[04010SS-05N-AT-00](#)