

Detailed Specifications

Frame Width:	40[mm]
Frame Height:	40[mm]
Frame Depth:	15[mm]
Max. Air Flow:	6.4[CFM]
Max. Air Flow:	0.18[m3 per min]
Max. Static Pressure:	0.21[In H2O]
Max. Static Pressure:	52[Pa]
Fan Speed:	7300[RPM]
Noise:	29[dB]
Life Expectancy:	40 degree C 40,000 Hours[L10]
Bearing Type:	Sleeve Bearing
Nominal Voltage:	24[V]
Operating Voltage 0 Lower:	10[V]
Operating Voltage 0 Upper:	25.2[V]
Current:	0.04[A]
Input Power:	1[W]
Mass:	23[g]
Tach / Locked Rotor Output:	Locked Rotor

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[04015SS-24M-AL-00](#)