

## Detailed Specifications

|                                    |                               |
|------------------------------------|-------------------------------|
| <b>Frame Width:</b>                | 40[mm]                        |
| <b>Frame Height:</b>               | 40[mm]                        |
| <b>Frame Depth:</b>                | 15[mm]                        |
| <b>Max. Air Flow:</b>              | 7.4[CFM]                      |
| <b>Max. Air Flow:</b>              | 0.21[m <sup>3</sup> per min]  |
| <b>Max. Static Pressure:</b>       | 0.27[In H <sub>2</sub> O]     |
| <b>Max. Static Pressure:</b>       | 68[Pa]                        |
| <b>Fan Speed:</b>                  | 8300[RPM]                     |
| <b>Noise:</b>                      | 32[dB]                        |
| <b>Life Expectancy:</b>            | 40 degree C 40,000 Hours[L10] |
| <b>Bearing Type:</b>               | Sleeve Bearing                |
| <b>Nominal Voltage:</b>            | 24[V]                         |
| <b>Operating Voltage - Lower:</b>  | 10[V]                         |
| <b>Operating Voltage - Upper:</b>  | 25.2[V]                       |
| <b>Current:</b>                    | 0.05[A]                       |
| <b>Input Power:</b>                | 1.2[W]                        |
| <b>Mass:</b>                       | 23[g]                         |
| <b>Tach / Locked Rotor Output:</b> | Locked Rotor                  |
| <b>Status:</b>                     | Active                        |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[04015SS-24N-AL-00](#)