

Detailed Specifications

Frame Width:	40[mm]
Frame Height:	40[mm]
Frame Depth:	20[mm]
Max. Air Flow:	8.4[CFM]
Max. Air Flow:	0.235[m3 per min]
Max. Static Pressure:	0.21[In H2O]
Max. Static Pressure:	54.2[Pa]
Fan Speed:	7500[RPM]
Noise:	29[dB]
Life Expectancy:	25 degree C 50,000 Hours (E00)[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	20[V]
Operating Voltage - Upper:	25.2[V]
Current:	0.27[A]
Input Power:	1.35[W]
Mass:	25[g]
Tach / Locked Rotor Output:	No
Status:	EOL

DC Axial Fans

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[04020KA-24M-AA-00](#)