

Detailed Specifications

Frame Width:	20[mm]
Frame Height:	45[mm]
Frame Depth:	45[mm]
Nominal Voltage:	12[V]
Max. Air Flow:	4.2[CFM]
Max. Static Pressure:	0.4[In H2O]
Speed:	6000[min-1]
Noise:	27[dB]
Life Expectancy:	25 degree C 50,000 Hours[L10]
Bearing Type:	Sleeve Bearing
Operating Voltage Lower:	6[V]
Operating Voltage Upper:	13.8[V]
Nominal Current:	0.09[A]
Input Power:	1.08[W]
Mass:	25[g]
Status:	Active

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[04520GA-12L-AA-00](#)