

Detailed Specifications

Frame Width:	60[mm]
Frame Height:	60[mm]
Frame Depth:	25[mm]
Max. Air Flow:	14.5[CFM]
Max. Air Flow:	0.41[m3 per min]
Max. Static Pressure:	0.1[In H2O]
Max. Static Pressure:	26[Pa]
Fan Speed:	3000[RPM]
Noise:	17[dB]
Life Expectancy:	60 degree C 40,000 Hours AA/EA[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.06[A]
Input Power:	0.7[W]
Mass:	56[g]
Tach / Locked Rotor Output:	No
Status:	Active

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[06025SA-12K-EA-D0](#)