

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	38[mm]
Max. Air Flow:	152.5[CFM]
Max. Air Flow:	4.32[m3 per min]
Max. Static Pressure:	1.2[In H2O]
Max. Static Pressure:	300[Pa]
Fan Speed:	7200[RPM]
Noise:	62.5[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	48[V]
Operating Voltage - Lower:	36[V]
Operating Voltage - Upper:	52.8[V]
Current:	0.57[A]
Input Power:	27.4[W]
Mass:	230[g]
Tach / Locked Rotor Output:	No
Status:	PCN

DC Axial Fans

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[09238RA-48Q-EA-00](#)