

Detailed Specifications

Frame Width:	119[mm]
Frame Height:	119[mm]
Frame Depth:	38[mm]
Max. Air Flow:	181.16[CFM]
Max. Air Flow:	5.13[m3 per min]
Max. Static Pressure:	0.86[In H2O]
Max. Static Pressure:	213[Pa]
Fan Speed:	4700[RPM]
Noise:	59.5[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage 0 Lower:	15[V]
Operating Voltage 0 Upper:	27.6[V]
Current:	0.93[A]
Input Power:	22.4[W]
Mass:	400[g]
IP Rating:	IP68/IP69K
Tach / Locked Rotor Output:	No

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[11938MA-24P-GA-00](#)