

Detailed Specifications

Frame Width:	30[mm]
Frame Height:	30[mm]
Frame Depth:	10[mm]
Max. Air Flow:	2.7[CFM]
Max. Air Flow:	0.078[m3 per min]
Max. Static Pressure:	0.116[In H2O]
Max. Static Pressure:	29[Pa]
Fan Speed:	7500[RPM]
Noise:	21[dB]
Bearing Type:	Ball Bearing
Nominal Voltage:	5[V]
Operating Voltage - Lower:	4.5[V]
Operating Voltage - Upper:	5.5[V]
Current:	0.1[A]
Input Power:	0.5[W]
Mass:	8.5[g]
Tach / Locked Rotor Output:	Locked Rotor

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[1204KL-01W-B39-B00](#)