

Detailed Specifications

Frame Width:	150[mm]
Frame Height:	172[mm]
Frame Depth:	50[mm]
Max. Air Flow:	346[CFM]
Max. Air Flow:	9.8[m3 per min]
Max. Static Pressure:	1.25[In H2O]
Max. Static Pressure:	312[Pa]
Fan Speed:	4600[RPM]
Noise:	68[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	48[V]
Operating Voltage - Lower:	38[V]
Operating Voltage - Upper:	52.8[V]
Current:	0.9[A]
Input Power:	43.2[W]
Mass:	870[g]
Tach / Locked Rotor Output:	No
Status:	Active

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[15050VA-48R-GA-00](#)