

Detailed Specifications

Frame Width:	40[mm]
Frame Height:	40[mm]
Frame Depth:	20[mm]
Max. Air Flow:	8.8[CFM]
Max. Air Flow:	0.25[m3 per min]
Max. Static Pressure:	0.24[In H2O]
Max. Static Pressure:	58.8[Pa]
Fan Speed:	7500[RPM]
Noise:	29[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	7[V]
Operating Voltage - Upper:	13.2[V]
Current:	0.08[A]
Input Power:	1[W]
Mass:	40[g]
Tach / Locked Rotor Output:	Tach Output

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[1608VL-04W-B49-B50](#)