

Detailed Specifications

Frame Width:	40[mm]
Frame Height:	40[mm]
Frame Depth:	20[mm]
Max. Air Flow:	10.2[CFM]
Max. Air Flow:	0.29[m3 per min]
Max. Static Pressure:	0.31[In H2O]
Max. Static Pressure:	76.6[Pa]
Fan Speed:	8500[RPM]
Noise:	31.4[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	14[V]
Operating Voltage - Upper:	26.4[V]
Current:	0.07[A]
Input Power:	1.7[W]
Mass:	40[g]
Tach / Locked Rotor Output:	No
Status:	PCN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[1608VL-05W-B50-B00](#)