

Detailed Specifications

| | |
|------------------------------------|--------------------------------|
| Frame Width: | 40[mm] |
| Frame Height: | 40[mm] |
| Frame Depth: | 20[mm] |
| Max. Air Flow: | 11.3[CFM] |
| Max. Air Flow: | 0.32[m3 per min] |
| Max. Static Pressure: | 0.4[In H2O] |
| Max. Static Pressure: | 99.3[Pa] |
| Fan Speed: | 9500[RPM] |
| Noise: | 34.6[dB] |
| Life Expectancy: | 25 degree C 100,000 Hours[L10] |
| Bearing Type: | Ball Bearing |
| Nominal Voltage: | 24[V] |
| Operating Voltage - Lower: | 14[V] |
| Operating Voltage - Upper: | 26.4[V] |
| Current: | 0.1[A] |
| Input Power: | 2.4[W] |
| Mass: | 40[g] |
| Tach / Locked Rotor Output: | Locked Rotor |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[1608VL-05W-B69-B00](#)