

Detailed Specifications

Frame Width:	172[mm]
Frame Height:	172[mm]
Frame Depth:	40[mm]
Max. Air Flow:	128.2[CFM]
Max. Air Flow:	3.63[m3 per min]
Max. Static Pressure:	0.12[In H2O]
Max. Static Pressure:	30.7[Pa]
Fan Speed:	1550[RPM]
Noise:	33.5[dB]
Life Expectancy:	-25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage 0 Lower:	10[V]
Operating Voltage 0 Upper:	13.2[V]
Current:	0.16[A]
Input Power:	1.9[W]
Mass:	325[g]
Tach / Locked Rotor Output:	No

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[17240JA-12M-YA-00](#)