

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	15[mm]
Max. Air Flow:	23.3[CFM]
Max. Air Flow:	0.66[m3 per min]
Max. Static Pressure:	0.06[In H2O]
Max. Static Pressure:	16[Pa]
Fan Speed:	2200[RPM]
Noise:	26[dB]
Life Expectancy:	25 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.11[A]
Input Power:	1.3[W]
Mass:	50[g]
Tach / Locked Rotor Output:	Locked Rotor
Status:	EOL

DC Axial Fans

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[3106KL-04W-B39-B00](#)