

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	25[mm]
Max. Air Flow:	35.5[CFM]
Max. Air Flow:	1[m3 per min]
Max. Static Pressure:	0.13[In H2O]
Max. Static Pressure:	32.3[Pa]
Fan Speed:	3000[RPM]
Noise:	31[dB]
Life Expectancy:	25 degree C 50,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	10[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.1[A]
Input Power:	2.4[W]
Mass:	95[g]
Tach / Locked Rotor Output:	No
Status:	EOL

DC Axial Fans

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[3110KL-05W-B40-E00](#)