

Detailed Specifications

Frame Width:	80[mm]
Frame Height:	80[mm]
Frame Depth:	25[mm]
Nominal Voltage:	115[V]
Frequency:	50[Hz]
Max. Air Flow:	16.2[CFM]
Max. Air Flow:	0.46[m3 per min]
Max. Static Pressure:	0.15[In H2O]
Max. Static Pressure:	39.2[Pa]
Fan Speed:	2600[RPM]
Noise:	28[dB]
Life Expectancy:	25deg.C 50,000 hours[L10]
Bearing Type:	Ball Bearing
Ingress Protection:	none
Starting Voltage:	65[V]
Input Power (+10% - 20%):	6[V]
Current:	0.09[A]
Mass:	220[g]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[3110PS-12W-B30-A00](#)