

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	25[mm]
Max. Air Flow:	33.5[CFM]
Max. Air Flow:	0.95[m3 per min]
Max. Static Pressure:	0.09[In H2O]
Max. Static Pressure:	21.5[Pa]
Fan Speed:	2050[RPM]
Noise:	22[dB]
Life Expectancy:	60 degree C 40,000 Hours AA/EA[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.07[A]
Input Power:	0.8[W]
Mass:	95[g]
Tach / Locked Rotor Output:	No
Status:	PCN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[3610SB-04W-B20-B00](#)