

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	25[mm]
Max. Air Flow:	51.2[CFM]
Max. Air Flow:	1.45[m3 per min]
Max. Static Pressure:	0.18[In H2O]
Max. Static Pressure:	45[Pa]
Fan Speed:	3100[RPM]
Noise:	32[dB]
Life Expectancy:	60 degree C 40,000 Hours AA/EA[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage 0 Lower:	12[V]
Operating Voltage 0 Upper:	26.4[V]
Current:	0.08[A]
Input Power:	1.9[W]
Mass:	95[g]
Tach / Locked Rotor Output:	No

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[3610SB-05W-B50-E00](#)