

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	25[mm]
Max. Air Flow:	54[CFM]
Max. Air Flow:	1.53[m3 per min]
Max. Static Pressure:	0.2[In H2O]
Max. Static Pressure:	50[Pa]
Fan Speed:	3200[RPM]
Noise:	35.5[dB]
Life Expectancy:	60 degree C 40,000 Hours AA/EA[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	7[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.18[A]
Input Power:	2.2[W]
Mass:	135[g]
Tach / Locked Rotor Output:	Tach Output

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[3610VL-04W-B29-B50](#)