

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	25[mm]
Max. Air Flow:	61.1[CFM]
Max. Air Flow:	1.73[m3 per min]
Max. Static Pressure:	0.26[In H2O]
Max. Static Pressure:	65[Pa]
Fan Speed:	3600[RPM]
Noise:	38.5[dB]
Life Expectancy:	60 degree C 40,000 Hours AA/EA[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	7[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.24[A]
Input Power:	2.9[W]
Mass:	135[g]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[3610VL-04W-B39-E00](#)