

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	25[mm]
Max. Air Flow:	68.1[CFM]
Max. Air Flow:	1.93[m3 per min]
Max. Static Pressure:	0.32[In H2O]
Max. Static Pressure:	80[Pa]
Fan Speed:	4000[RPM]
Noise:	42[dB]
Life Expectancy:	60 degree C 40,000 Hours AA/EA[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	14[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.17[A]
Input Power:	4.1[W]
Mass:	135[g]
Tach / Locked Rotor Output:	Tach Output

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[3610VL-05W-B49-E50](#)