

## Detailed Specifications

|                                    |                                     |
|------------------------------------|-------------------------------------|
| <b>Frame Width:</b>                | 92[mm]                              |
| <b>Frame Height:</b>               | 92[mm]                              |
| <b>Frame Depth:</b>                | 25[mm]                              |
| <b>Max. Air Flow:</b>              | 96.4[CFM]                           |
| <b>Max. Air Flow:</b>              | 2.73[m3 per min]                    |
| <b>Max. Static Pressure:</b>       | 0.6[In H2O]                         |
| <b>Max. Static Pressure:</b>       | 150[Pa]                             |
| <b>Fan Speed:</b>                  | 5600[RPM]                           |
| <b>Noise:</b>                      | 51[dB]                              |
| <b>Life Expectancy:</b>            | 60 degree C 40,000 Hours AA/EA[L10] |
| <b>Bearing Type:</b>               | Ball Bearing                        |
| <b>Nominal Voltage:</b>            | 24[V]                               |
| <b>Operating Voltage 0 Lower:</b>  | 14[V]                               |
| <b>Operating Voltage 0 Upper:</b>  | 27.6[V]                             |
| <b>Current:</b>                    | 0.38[A]                             |
| <b>Input Power:</b>                | 9.1[W]                              |
| <b>Mass:</b>                       | 135[g]                              |
| <b>Tach / Locked Rotor Output:</b> | Locked Rotor                        |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[3610VL-05W-B79-E00](#)