

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	32[mm]
Max. Air Flow:	58.6[CFM]
Max. Air Flow:	1.66[m3 per min]
Max. Static Pressure:	0.24[In H2O]
Max. Static Pressure:	61[Pa]
Fan Speed:	3200[RPM]
Noise:	38[dB]
Life Expectancy:	25 degree C 100,000 Hours[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage 0 Lower:	6[V]
Operating Voltage 0 Upper:	13.8[V]
Current:	0.31[A]
Input Power:	3.7[W]
Mass:	230[g]
Tach / Locked Rotor Output:	Locked Rotor

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[3612KL-04W-B49-B00](#)