

Detailed Specifications

Frame Width:	119[mm]
Frame Height:	119[mm]
Frame Depth:	25[mm]
Max. Air Flow:	88.2[CFM]
Max. Air Flow:	2.5[m3 per min]
Max. Static Pressure:	0.13[In H2O]
Max. Static Pressure:	32.3[Pa]
Fan Speed:	2200[RPM]
Noise:	35[dB]
Life Expectancy:	25 degree C 100,000 Hours (B00 / E00) [L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	12[V]
Operating Voltage - Lower:	6[V]
Operating Voltage - Upper:	13.8[V]
Current:	0.28[A]
Input Power:	3.4[W]
Mass:	180[g]
Tach / Locked Rotor Output:	No

DC Axial Fans

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[4710KL-04W-B30-B00](#)