

Detailed Specifications

Frame Width:	119[mm]
Frame Height:	119[mm]
Frame Depth:	25[mm]
Max. Air Flow:	75.9[CFM]
Max. Air Flow:	2.15[m3 per min]
Max. Static Pressure:	0.1[In H2O]
Max. Static Pressure:	24.8[Pa]
Fan Speed:	1900[RPM]
Noise:	31[dB]
Life Expectancy:	25 degree C 100,000 Hours (B00 / E00) [L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage 0 Lower:	10[V]
Operating Voltage 0 Upper:	27.6[V]
Current:	0.1[A]
Input Power:	2.4[W]
Mass:	180[g]
Tach / Locked Rotor Output:	Tach Output

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[4710KL-05W-B29-E50](#)