

Detailed Specifications

Frame Width:	119[mm]
Frame Height:	119[mm]
Frame Depth:	25[mm]
Max. Air Flow:	114.7[CFM]
Max. Air Flow:	3.25[m3 per min]
Max. Static Pressure:	0.2[In H2O]
Max. Static Pressure:	50.5[Pa]
Fan Speed:	2800[RPM]
Noise:	41.5[dB]
Life Expectancy:	25 degree C 100,000 Hours (B00 / E00) [L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	10[V]
Operating Voltage - Upper:	26[V]
Current:	0.29[A]
Input Power:	7[W]
Mass:	180[g]
Tach / Locked Rotor Output:	Tach Output

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[4710KL-05W-B59-E50](#)