

Detailed Specifications

Frame Width:	119[mm]
Frame Height:	119[mm]
Frame Depth:	38[mm]
Nominal Voltage:	115[V]
Frequency:	60[Hz]
Max. Air Flow:	70[CFM]
Max. Air Flow:	1.98[m3 per min]
Max. Static Pressure:	0.12[In H2O]
Max. Static Pressure:	30[Pa]
Fan Speed:	1900[RPM]
Noise:	33[dB]
Life Expectancy:	25deg.C 100,000 hours[L10]
Bearing Type:	Ball Bearing
Ingress Protection:	none
Starting Voltage:	75[V]
Input Power (+10% - 20%):	10[V]
Current:	0.11[A]
Mass:	550[g]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[4715FS-12T-B10-D00](#)