

Detailed Specifications

Frame Width:	150[mm]
Frame Height:	172[mm]
Frame Depth:	25.4[mm]
Max. Air Flow:	290[CFM]
Max. Air Flow:	8.2[m3 per min]
Max. Static Pressure:	0.89[In H2O]
Max. Static Pressure:	233[Pa]
Fan Speed:	4100[RPM]
Noise:	65.4[dB]
Bearing Type:	Ball Bearing
Nominal Voltage:	48[V]
Operating Voltage 0 Lower:	25[V]
Operating Voltage 0 Upper:	60[V]
Current:	0.74[A]
Input Power:	35.5[W]
Mass:	510.3[g]
Tach / Locked Rotor Output:	No

DC Axial Fans

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[5910PL-07W-B70-L00](#)