

Detailed Specifications

Frame Width:	150[mm]
Frame Height:	172[mm]
Frame Depth:	50.8[mm]
Max. Air Flow:	260[CFM]
Max. Air Flow:	7.36[m3 per min]
Max. Static Pressure:	0.73[In H2O]
Max. Static Pressure:	182.75[Pa]
Fan Speed:	3500[RPM]
Noise:	60.3[dB]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage 0 Lower:	12[V]
Operating Voltage 0 Upper:	30[V]
Current:	0.79[A]
Input Power:	19[W]
Mass:	830[g]
Tach / Locked Rotor Output:	No

DC Axial Fans

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[5920PL-05W-B50-D00](#)