

Detailed Specifications

Frame Size:	75[mm]
Frame Width:	30[mm]
Nominal Voltage:	24[V]
Max. Air Flow:	8.8[CFM]
Max. Static Pressure:	0.3[In H2O]
Speed:	2550[min^{-1}]
Noise:	34.5[dB]
Life Expectancy:	25 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Operating Voltage Lower:	10[V]
Operating Voltage Upper:	27.6[V]
Nominal Current:	0.09[A]
Input Power:	2.16[W]
Mass:	90[g]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[BG0703-B053-00L-00](#)