

Detailed Specifications

Frame Size:	75[mm]
Frame Width:	30[mm]
Nominal Voltage:	24[V]
Max. Air Flow:	10.5[CFM]
Max. Static Pressure:	0.44[In H2O]
Speed:	3000[min^{-1}]
Noise:	38.5[dB]
Life Expectancy:	25 degree C 70,000 Hours[L10]
Bearing Type:	Ball Bearing
Operating Voltage Lower:	10[V]
Operating Voltage Upper:	26[V]
Nominal Current:	0.15[A]
Input Power:	3.6[W]
Mass:	90[g]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[NMB Technologies:](#)

[BG0703-B054-00S-00](#)